



PRODUCT SPECIFICATION

2.5" TS80 Nanofiltration Element Series


Lenntech bv
Rotterdamseweg 402m
2629HH Delft
info@lenntech.com
www.lenntech.com
Tel. +31-15-261.09.00
Fax. +31-15-261.62.89

Model	Permeate flow GPD (m3/day)*	Average Salt Rejection (%)	Minimum Salt Rejection (%)
2540-TS80-TSF	650 (2.0)	99.00	97.00

Performance is based on the following test conditions: 2,000.0 ppm MgSO₄, 110.0 psi, 25°C, 15% recovery, pH 8.0, 30 minutes operation.

OPERATIONAL AND DESIGN DATA

Membrane Type.....	ANM Aromatic Polyamide Advanced Nanofiltration Membrane
Configuration.....	Spiral Wound, Fiberglass Outer Wrap
Active Membrane Area.....	26 ft ² (2.4 m ²)
Recommended Applied Pressure.....	40 - 200 psi (3 - 14 bar)
Maximum Applied Pressure.....	600 psi (41 bar)
Recommended Operating Temperature.....	35 - 113°F (2 - 45°C)
Feedwater pH Range.....	2 - 11 continuous
Chlorine Tolerance.....	<0.1 ppm
Maximum Feed Flow.....	6 GPM (1.4 m ³ /hr)
Minimum Brine Flow/Permeate Flow Ratio....	5:1
Maximum SDI (15 minutes)	5.0
Maximum Turbidity.....	1 NTU



Element Weight : 7 (3.2)
Length (A) : 40.0 (1,016) Diameter (B) : 2.5 (63) Permeate Tube (C) : 0.75 (19.1)
Units in pounds and inches, units in paranthesis in kilograms and millimetres.
Mechanical Configuration: Filmtec Style Core Tube
Feed Spacer: 0.031" thick diamond spacer

* Permeate flow is clean water flux at standard conditions above. Not applicable for all feedwater conditions. Individual element's permeate flow may vary +/- 15%.



Engineered Membrane
SOLUTIONS