

Lewatit® MonoPlus MP 800 is a strongly basic, macroporous anion exchange resin (type I) with beads of uniform size (monodisperse) based on a styrene-divinylbenzene copolymer, designed for all demineralization applications.

The monodisperse beads have high chemical and osmotic stability. The extremely high monodispersity and very low fines content result in particularly low pressure losses compared with standard resins. Due to its special macroporous structure

Lewatit® MonoPlus MP 800 stands for effective adsorption and desorption of naturally occurring organic substances.

Lewatit® MonoPlus MP 800 is especially applicable for:

- » the demineralization of water for industrial steam generation, e.g. Lewatit® WS System, Lewatit® Liftbed System or Lewatit® Rinsebed System
- » polishing using the Lewatit® Multistep System or a conventional mixed bed arrangement in combination with **Lewatit® MonoPlus SP 112 (H)**
- » condensate polishing in combination with **Lewatit® MonoPlus SP 112 (H)**

Lewatit® MonoPlus MP 800 adds special features to the resin bed:

- » high flow rates during regeneration and loading
- » a good utilization of the total capacity
- » low rinse water requirement
- » homogeneous throughput of regenerants, water and solutions, resulting in a homogeneous operating zone
- » virtually linear pressure drop gradient across the entire bed depth, allowing operation with higher bed depths
- » good separation of the components in mixed bed applications

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies.

Common Description

Delivery form	Cl ⁻
Functional group	Quaternary ammonium Type 1
Matrix	Styrenic
Structure	Macroporous
Appearance	Beige, opaque

Specified Data

Uniformity coefficient		max.	1.1
Mean bead size	d50	mm	0.62 (+/-0.05)
Total capacity (delivery form)		min. eq/L	1.0

Typical Physical and Chemical Properties

Bulk density for shipment	(+/- 5%)	g/L	620
Density		approx. g/mL	1.06
Water retention (delivery form)		approx. weight %	63-68
Volume change (Cl ⁻ -OH ⁻)		max. approx. %	22
Stability pH range			0-14
Storage time (after delivery)		max. years	2
Storage temperature range		°C	-20 - +40

Operation

Operating temperature		max. °C	70
Operating pH range	during exhaustion		0-12
Bed depth for single column		min. mm	800
Bed depth per component in mixed bed		min. mm	500
Back wash bed expansion per m/h (20°C)		%	19
Specific pressure loss kPa*h/m ² (15°C)		kPa*h/m ² (15°C)	0.8
Max. pressure loss during operation		kPa	300
Specific flow rate		max. BV/h	100

Regeneration

NaOH regeneration	concentration	approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. g/L resin	80
NaOH regeneration	quantity counter-current	min. g/L resin	50
Regeneration contact time		min. minutes	20
Slow rinse at regeneration flow rate		min. BV	2
Fast rinse at service flow rate		min. BV	2

This document contains important information and must be read in its entirety.

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described above. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

This document contains important information
and must be read in its entirety.



WATER TREATMENT SOLUTIONS

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

For more information or a quote, please use the