

Lewatit® S 5328 is a food grade, gelular acrylic medium base (bifunctional) anion exchange resin.

Due to its acrylic structure **Lewatit® S 5328** stands for effective adsorption and desorption of naturally occurring organic substances (high resistance to organic fouling). The very high total capacity and outstanding mechanical stability together with the excellent resistance to osmotic shock makes it unique for demineralization applications.

Lewatit® S 5328 is especially suitable for the following applications:

- Demineralization of aqueous solutions such as gelatine, fruit juices, whey and food acids operated with co-current or modern counter-current systems like e.g. Lewatit® WS System
- the removal of organic matter

When using **Lewatit® S 5328** to treat potable water and the aqueous solutions listed above, special care should be given to the start up conditions of the new resin. Please refer to the recommended start-up conditions available on request.

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies.

Common Description

Delivery form	Free base/Cl ⁻
Functional group	Tertiary amine / quaternary ammonium
Matrix	Acrylic
Structure	Gel
Appearance	Ivory, opaque

Specified Data

Uniformity coefficient		max.	1.8
Range of size for >90 vol% of all beads		mm	0.4-1.6
Effective size	d10	mm	0.50-0.75
Fines	less than 0.315 mm	max. vol %	0.5
Total capacity (delivery form)		min. eq/L	1.25

Typical Physical and Chemical Properties

Bulk density for shipment	(+/- 10%)	g/L	710
Density		approx. g/mL	1.06
Water retention (delivery form)		approx. weight %	56-64
Volume change (free base - Cl)		max. approx. %	14
Stability pH range			0-14
Stability temperature range		°C	1-35
Storage time (after delivery)		max. years	2
Storage temperature range		°C	-20 - +40

Operation

Operating temperature		max. °C	35
Operating pH range	during exhaustion		0-12
Bed depth for single column		min. mm	800
Back wash bed expansion per m/h (20°C)		%	12
Specific pressure loss kPa*h/m ² (15°C)		kPa*h/m ² (15°C)	1.1
Max. pressure loss during operation		kPa	150
Specific flow rate		max. BV/h	5
Freeboard	during backwash	min. vol. %	80-100

Regeneration

NaOH regeneration	concentration	approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. g/L resin	100
NaOH regeneration	quantity counter-current	min. g/L resin	70
Regeneration contact time		min. minutes	30
Slow rinse at regeneration flow rate		min. BV	2
Fast rinse at service flow rate		min. BV	4

This document contains important information and must be read in its entirety.

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described above. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

This document contains important information
and must be read in its entirety.



WATER TREATMENT SOLUTIONS

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

For more information or a quote, please use the