

LENNTECH

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

Micro-Klean™ D Series Depth Filter Cartridges

A different filter cartridge

Micro-Klean™ D Series filter cartridges, formerly known as CUNO Micro-Wynd, are produced by a special 3M Purification process which combines 2 separate materials simultaneously on a common core.

The filtering media is applied in blanket form whilst the matrix is wound spirally under controlled tension to bind the media blanket in a firm position.

The winding pattern creates wide diamond shaped chambers which provides the exceptional performances in flow and life time of the Micro-Klean D filter cartridges. With the ordinary wound filter cartridge, there is no distinct filtering media, the matrix only is operating. It is brushed and separate during the winding operation. This accounts for the shortness of fibres and lack of the very important necessary quantity of matrix, which shortens considerably the life and lowers flow rates.

Multi-length cartridges

To eliminate any chance of by-pass at the cartridge joints, Micro-Klean D filter cartridges can be delivered in several lengths but in one piece construction from 9 3/4" to 29". In this case, the media blanket is continuous on the whole length of the cartridge, eliminating overlap winding joints. Integral length cartridges also assure easier and shorter change out.

Operating conditions

Micro-Klean D filter cartridges are nominally rated (from 1 µm to 150 µm nominal). Maximum service temperature can be up to 120 °C depending on the material selected (refer to the specifications of each type). Maximum differential pressure is 5 bar, but it is recommended to replace them at 2.5 bar.



Regulatory compliance

Standard Micro-Klean™ D Series filter cartridges comply with the requirements of Regulation (EC) 1935/2004 for their intended food contact applications. All materials of construction are listed in the FDA CFR Title 21. Contact 3M Purification for further information.

Features and benefits

Flow capacity up to 3 times higher than the conventional string-wound cartridges

- Reduces total filtration costs

Dirt holding capacity up to twice greater

- Reduces total filtration costs

Mechanically able to withstand a very high differential pressure

- Reduces total filtration costs

High dirt removal efficiency

- Reduces total filtration costs

Longer life time

- Less maintenance and production down time
- Decreases waste management costs

Approved for food contact use

-  Standard cartridges comply with European and US regulations

Applications

Industrial

- Water
- Acids
- Solvents
- Chemical products, etc. ...

Food and Beverage

- Ready-to-drink beverages
- Juices
- Alcoholic beverages
- Dairy products
- Process and blending water

3M

Micro-Klean™ D Series filter cartridges - Ordering guide

PPP TYPE			
Nominal Micron rating (micron)	Simple length (250 mm)	Double length (500 mm)	Triple length (750 mm)
1	D-PPPY	D-PPPY-2	D-PPPY-3
3	D-PPPA	D-PPPA-2	D-PPPA-3
5	D-PPPB	D-PPPB-2	D-PPPB-3
10	D-PPPC	D-PPPC-2	D-PPPC-3
25	D-PPPF	D-PPPF-2	D-PPPF-3
50	D-PPPL	D-PPPL-2	D-PPPL-3
75/150	D-PPPHD	D-PPPHD-2	D-PPPHD-3

CCS TYPE			
Nominal Micron rating (micron)	Simple length (250 mm)	Double length (500 mm)	Triple length (750 mm)
1	D-CCSY	D-CCSY-2	D-CCSY-3
3	D-CCSA	D-CCSA-2	D-CCSA-3
5	D-CCSB	D-CCSB-2	D-CCSB-3
10	D-CCSC	D-CCSC-2	D-CCSC-3
25	D-CCSF	D-CCSF-2	D-CCSF-3
50	D-CCSL	D-CCSL-2	D-CCSL-3
75/150	D-CCSHD	D-CCSHD-2	D-CCSHD-3

CCT TYPE			
Nominal Micron rating (micron)	Simple length (250 mm)	Double length (500 mm)	Triple length (750 mm)
1	D-CCTY	D-CCTY-2	D-CCTY-3
3	D-CCTA	D-CCTA-2	D-CCTA-3
5	D-CCTB	D-CCTB-2	D-CCTB-3
10	D-CCTC	D-CCTC-2	D-CCTC-3
25	D-CCTF	D-CCTF-2	D-CCTF-3
50	D-CCTL	D-CCTL-2	D-CCTL-3
75/150	D-CCTHD	D-CCTHD-2	D-CCTHD-3

Several configurations are possible in combining different materials of the media, matrix and core. Micro-Klean D filter cartridges are available in standard length from 9 3/4" to 29" (integral length) and in DOE version. Longer length (i.e. 40") or SOE versions (with end caps and double O-ring) can be produced upon request.

Depending on the chemical compatibility requested by the application, different configurations can be chosen. However, it is always recommended to check the chemical compatibility by a soaking test in the liquid to be filtered.

Standard filter cartridge types

PPP TYPE

- Polypropylene media, matrix and core.
- Cartridge for applications involving strong acid, concentrated alkalis, strong oxidising and reducing agents, electroplating and other chemicals in aqueous solutions.
- Not suitable for hydrocarbon type solvents such as hexane, naphtha, petroleum, ether, etc. Maximum service temperature: 80 °C (60 °C for double and triple lengths).

CCS TYPE

- Cotton media and matrix, 304 stainless steel core.
- Proposed for general fluid applications. Temperature up to 120 °C - dilute acids (1%), dilute alkalis (5%). For gases, the temperature must not exceed 100 °C.

CCT TYPE

- Cotton media and matrix, 316 stainless steel core.
- Proposed for all general fluids at temperature rating up to 120 °C. For gases, temperature must not exceed 100 °C.
- Same applications as for the CCS but greater chemical resistance of the core to acids and alkalis.

Special filter cartridge types

Other materials combinations can be produced on request with minimum order quantities, particularly the following types:

- D-PPS: polypropylene media and matrix, 304 SS core
- D-PPT: polypropylene media and matrix, 316 SS core
- D-CCP: cotton media and matrix, polypropylene core
- D-CCF: cotton media and matrix, tinned steel core.

Note: Micro-Klean D is new name of CUNO Micro-Wynd.

Important Notice

The information described in this literature is accurate to the best of our knowledge. A variety of factors, however, can affect the performance of the Product(s) in a particular application, some of which are uniquely within your knowledge and control. INFORMATION IS SUPPLIED UPON THE CONDITION THAT THE PERSONS RECEIVING THE SAME WILL MAKE THEIR OWN DETERMINATION AS TO ITS SUITABILITY FOR THEIR USE. IN NO EVENT WILL 3M PURIFICATION BE RESPONSIBLE FOR DAMAGES OF ANY NATURE WHATSOEVER RESULTING FROM THE USE OF OR RELIANCE UPON INFORMATION.

It is your responsibility to determine if additional testing or information is required and if this product is fit for a particular purpose and suitable in your specific application.

3M PURIFICATION MAKES NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESS OR IMPLIED INCLUDING WITHOUT LIMITATION ANY WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE HEREUNDER WITH RESPECT TO INFORMATION OR THE PRODUCT TO WHICH INFORMATION REFERS.

Limitation of Liability

3M Purification will not be liable for any loss or damage arising from the use of the Product(s), whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation may not apply to you.



LENNTECH

info@lenntech.com Tel. +31-152-610-900
www.lenntech.com Fax. +31-152-616-289

3M is a registered trademark of the 3M Company. Micro-Klean is a registered trademark of the 3M Company used under license.

Data may be subject to change without further notice.

© 3M 2012. All rights reserved.