

JX series

industrial microfiltration elements for stream clarification

The J-Series family of microfiltration membrane elements is used for process stream clarification including suspended solids removal.


The J-Series membrane is manufactured with a pore-size of 0.3 micron.

Table 1: Element Specification

Membrane	J-Series, Polyvinylidene Fluoride
----------	-----------------------------------

Model	Spacer mil (mm)	Active area ft² (m²)	Outer wrap	Part number
JX2540F30	30 (0.76)	28 (2.6)	Fiberglass	1207253
JX2540F50	50 (1.27)	22 (2.0)	Fiberglass	1207252
JX4040C30	30 (0.76)	82 (7.6)	Cage	1207264
JX4040F30	30 (0.76)	79 (7.3)	Fiberglass	3049975
JX4040F50	50 (1.27)	62 (5.8)	Fiberglass	3049974
JX8040F30	30 (0.76)	340 (31.6)	Fiberglass	1207283
JX8040F50	50 (1.27)	269 (25.0)	Fiberglass	1207284

Water Technologies & Solutions fact sheet



Note: 4040C elements do not feature brine seal

Figure 1: Element Dimensions Diagram – Female




Figure 2: Element Dimensions Diagram – Male

Table 2: Dimensions and Weight

Model	Type	Dimensions, inches (cm)			Boxed Weight lbs (kg)
		A	B	C	
JX2540F**	Male	40.0 (101.6)	0.75 1.90	2.4 (6.1)	4 (1.8)
JX4040C**	Female	40.0 (101.6) (1)	0.625 (1.59)	3.9 (9.9)	9 (4.1)
JX4040F**	Male	40.0 (101.6)	0.75 (1.90)	3.9 (9.9)	9 (4.1)
JX8040F**	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	29 (13.2)

(1) Includes interconnector, refer to Technical Bulletin TB1206.

LENNTECH

info@lennotech.com Tel. +31-152-610-900
www.lennotech.com Fax. +31-152-616-289

Table 3: Operating and CIP parameters

Typical Operating Flux	5-20 GFD (8-34 LMH)
Maximum Operating Pressure	100psi (700kPa)
Maximum Temperature	Continuous Operation: 122°F (50°C) Clean-In-Place (CIP): 122°F (50°C)
pH Range	Continuous Operation: 2.0-10.0 Clean-In-Place (CIP): 1.0-13.0 (1)
Maximum Pressure Drop	Over an element: 15 psi (103 kPa) Per housing: 60 psi (414 kPa)
Chlorine Tolerance	5,000+ ppm-days

(1) Refer to Cleaning Guidelines Technical Bulletin TB1194.

LENNTECH

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289