

AMBERSEP™ GT74

Industrial Grade Complexing Resin

PRODUCT DATA SHEET

AMBERSEP GT74 is a weakly acidic cation exchange resin with very pronounced selectivity for certain metal ions, e.g. rhodium, copper, silver, cadmium and lead.

AMBERSEP GT74 has been developed for the removal of Hg from different solutions and gaseous streams and can be regenerated very efficiently with hydrochloric acid.

The selectivity sequence is :

Hg > Ag > Cu > Pb > Cd > Ni > Co > Fe > Ca > Na.

AMBERSEP GT74 is insoluble in common solvents and stable over the entire pH range. Oxidizing media should be avoided. The special properties of AMBERSEP GT74 can be useful for problems where removal of metal ions Cu, Ag, Pb, Cd is desired. Applications may be found in different fields of chemical technology such as waste water treatment, recovery of solutions and metals in the plating industry, reocovery of catalysts and removal of interfering ions in hydrometallurgy.

PROPERTIES

Matrix	Macroporous styrene copolymer
Functional groups	Thiol
Physical form	Beads
Ionic form as shipped	H
Total exchange capacity ^[1]	≥ 1.30 eq/L (SH form)
Moisture holding capacity ^[1]	48 to 55 % (H form)
Shipping weight	785 g/L (49.0 lb/ft ³)
Particle size	
Harmonic mean size	0.450 - 0.700 mm
Uniformity coefficient	≤ 1.8
Fines content ^[1]	< 0.425 mm : 12 % max
Coarse beads	> 0.850 mm : 15 % max

^[1] Contractual value

Test methods available upon request

SUGGESTED OPERATING CONDITIONS

Maximum operating temperature	60°C (140 °F)
Minimum bed depth	1 m (39 inches)
Service flow rate	10 BV/h (1.25 gpm/ft ³)
Regenerant	Concentrated hydrochloric acid
Rinse requirements	2 to 3 BV* (15 to 22.5 gal/ft ³)
Backwash flow rate	About 12 m/h (5 gpm/ft ²) with water at 20°C (68 °F)

* 1 BV (Bed Volume) = 1 m³ solution per m³ resin

SELECTIVITY


The high selectivity of AMBERSEP GT74 for certain metals is shown in the graph below as a function of pH. All data were determined in a normal solution of NaNO_3 . The resin has a pronounced preference for copper, lead and cadmium ions, which are removed in considerable quantities, even from solutions containing only 1 meq/L of metal and a large excess of Na^+ ions. The data indicate the possibility of selective separation of these metals.

Example : Removal of lead from waste water

Influent composition

- Pb^{++} 6 ppm
- Sb^{+++} 0.3 ppm
- Na^+ 100 ppm
- pH 2.5

The solution passes a column of AMBERSEP GT74 at a flow rate of 15 m/h (6 gpm/ft²). The effluent contains less than 0.01 ppm Pb. . After passage of 700 bed volumes of the solution the effluent composition was still unchanged.



All our products are produced in ISO 9001 certified manufacturing facilities.

ROHM AND HAAS 

AMBERJET is a trademark of Rohm and Haas Company and its affiliates, Philadelphia, U.S.A.

Ion exchange resins and polymeric adsorbents, as produced, contain by-products resulting from the manufacturing process. The user must determine the extent to which organic by-products must be removed for any particular use and establish techniques to assure that the appropriate level of purity is achieved for that use. The user must ensure compliance with all prudent safety standards and regulatory requirements governing the application. Except where specifically otherwise stated, Rohm and Haas Company does not recommend its ion exchange resins or polymeric adsorbents, as supplied, as being suitable or appropriately pure for any particular use. Consult your Rohm and Haas technical representative for further information. Acidic and basic regenerant solutions are corrosive and should be handled in a manner that will prevent eye and skin contact. Nitric acid and other strong oxidising agents can cause explosive type reactions when mixed with Ion Exchange resins. Proper design of process equipment to prevent rapid buildup of pressure is necessary if use of an oxidising agent such as nitric acid is contemplated. Before using strong oxidising agents in contact with Ion Exchange Resins, consult sources knowledgeable in the handling of these materials.

Rohm and Haas Company makes no warranties either expressed or implied as to the accuracy or appropriateness of these data and expressly excludes any liability upon Rohm and Haas arising out of its use. We recommend that the prospective users determine for themselves the suitability of Rohm and Haas materials and suggestions for any use prior to their adoption. Suggestions for uses of our products of the inclusion of descriptive material from patents and the citation of specific patents in this publication should not be understood as recommending the use of our products in violation of any patent or as permission or license to use any patents of the Rohm and Haas Company and its affiliates. Material Safety Data Sheets outlining the hazards and handling methods for our products are available on request.