

LENNTECH MO6 8" REVERSE OSMOSIS SYSTEM

APPLICATIONS

Process water, rinse water, steam boilers, heating and cooling circuits, agriculture, desalination, food and beverage, utility water treatment.

EQUIPMENT:

- Grundfos® CR 15-9 high pressure pump...1 pcs
- 8040-2 membrane vessel.....3 pcs
- BB20 sediment prefilter.....4 pcs
- Motorized valves.....2 pcs
(feed water in, flush out)
- Balancing valves.....2 pcs
(concentrate reject, concentrate recycle)
- Electrical cabinet with Ecosoft controller...1 set
- Piping, instrumentation, steel frame.....1 set



Lenntech reserves the right to amend the product's system architecture provided that its functionality and usability will not deteriorate

OPTIONS

- Filmtec™ XLE-440 / ECO PRO-440
- Dosing pump for antiscalant or other RO chemicals
- Permeate inlet for permeate membrane rinse
- Raw water mixing line

CONNECTION PORT SIZES:

Influent water.....G 2"
Permeate.....G 1½"
Concentrate.....G 2"
CIP inlet.....G 1½"
CIP return.....G 1½"
CIP permeate.....G 1"
Antiscalant dosing port.....G ½"

PHYSICAL PARAMETERS:

Approximate dimensions (bare).....2.90 × 1.20 × 1.95 m
(Width × Depth × Height, ±5%)
Approximate dimensions (crated).....3.05 × 1.37 × 2.24 m
(Width × Depth × Height, ±5%)
Approximate weight (bare).....560 kg
Approximate weight (crated).....720 kg

MO6 8" REVERSE OSMOSIS SYSTEM

Code	Product	Flow capacity, m³/h (GPH)	Membranes**
MO6TP5	MO6 RO System	6–8 (1 600–2 100)	6/80 x 40

** Membranes are not included


TECHNICAL SPECIFICATION

Permeate capacity ¹	6 m ³ /h
Permeate recovery ²	75%
Maximum TDS	3000 mg/L
Influent flow demand	8...12 m ³ /h (service) 20 m ³ /h (rinse)
Operating pressure	8...12 bar
Maximum pressure	14 bar
Electrical requirements	380...400 V, 50 Hz (3 ph)
Electrical power	7.5 kW
Prefilter rating	5 µm

¹ depends on feed water TDS, temperature, and permeate recovery — see graph on the right

² for low scaling/fouling water

MO6 RO FLOW CAPACITY GRAPH (WITH XLE-440 MEMBRANES)



Permeate flow rates are calculated under the following conditions:
 • 2 bar influent water pressure
 • 0 bar backpressure in the permeate line
 • fresh membranes
 • XLE-440 membrane

PIPES AND INSTRUMENTS DIAGRAM

