

CRI5-10 A-FGJ-I-E-HQQE 3x230/400 50HZ

Grundfos Pump 96528006



Thank you for your interest in our products


Please contact us for more information, or visit our website


<http://www.lenntech.com/grundfos/CRI05/96528006/CRI-5-10-A-FGJ-I-E-HQQE.html>

info@lenntech.com

tel. +31-15-261.09.00

fax. +31-15-261.62.89

Position	Qty.	Description
	1	CRI 5-10 A-FGJ-I-E-HQQE  Note! Product picture may differ from actual product Product No.: 96528006 Vertical, multistage centrifugal pump with suction and discharge ports on same the level (in-line) enabling installation in a horizontal one-pipe system. Pump materials in contact with the liquid are in stainless steel. A cartridge shaft seal ensures high reliability, safe handling and easy service and access. Power transmission is via a split coupling. Pipework connection is via combined DIN-ANSI-JIS flanges. The pump is fitted with a 3-phase, fan-cooled asynchronous motor. Further product details The product carries the Grundfos Blueflux[®] label. It represents the best from Grundfos within energy-efficient motors and frequency converters. Grundfos Blueflux[®] solutions either meet or exceed legislative requirements such as the EuP IE3 grade.  Steel, cast iron and aluminium components have an epoxy-based coating made in a cathodic electro-deposition (CED) process. CED is a high-quality dip-painting process where an electrical field around the products ensures deposition of paint particles as a thin, well-controlled layer on the surface. An integral part of the process is a pretreatment. The entire process consists of these elements: 1) Alkaline-based cleaning. 2) Zinc phosphating. 3) Cathodic electro-deposition. 4) Curing to a dry film thickness 18-22 my m. The colour code for the finished product is NCS 9000/RAL 9005. Pump A standard split coupling connects the pump and motor shaft. It is enclosed in the pump head/motor stool by means of two coupling guards.  The pump head and flange for motor mounting is made in one piece (cast iron). The pump head cover is a separate component (stainless steel). The pump head has a combined 1/2" priming plug and air vent screw.



The pump is fitted with a balanced O-ring seal unit with rigid torque transmission system. This seal type is assembled in a cartridge unit which makes replacement safe and easy. Due to the balancing, this seal type is suitable for high-pressure applications. The cartridge construction also protects the pump shaft from possible wear from a dynamic O-ring between pump shaft and shaft seal.


Primary seal:

- Rotating seal ring material: Silicon carbide (SiC)
- Stationary seat material: Silicon carbide (SiC)

This material pairing is used where higher corrosion resistance is required. The high hardness of this material pairing offers good resistance against abrasive particles.

Secondary seal material: EPDM (ethylene-propylene rubber)


EPDM has excellent resistance to hot water. EPDM is not suitable for mineral oils.



The shaft seal is screwed into the pump head.

The chambers and impellers are made of stainless steel sheet. The chambers are provided with a PTFE neck ring offering improved sealing and high efficiency. The impellers have smooth surface, and the shape of the blades ensure a high efficiency.

The pump has a stainless steel base mounted on a separate base plate. The base and base plate are kept in position by the tension of the staybolts which hold the pump together. The discharge side of the base has a combined drain plug and bypass valve. The pump is secured to the foundation by four bolts through the base plate. The flanges are fastened to the base by means of locking rings.



Motor

The motor is a totally enclosed, fan-cooled motor with principal dimensions to IEC and DIN standards. The motor is flange-mounted with tapped-hole flange (FT).


Motor mounting designation in accordance with IEC 60034-7: IM B 14 (Code I) / IM 3601 (Code II).
Electrical tolerances comply with IEC 60034.

The motor efficiency is classified as IE3 in accordance with IEC 60034-30.

Position	Qty.	Description
		The motor does not incorporate motor protection and must be connected to a motor-protective circuit breaker which can be manually reset. The motor-protective circuit breaker must be set according to the rated current of the motor (I_l/1). The motor can be connected to a variable speed drive for adjustment of pump performance to any duty point. Grundfos CUE offers a range of variable speed drives. Please find more information in Win-/WebCAPS. Technical data Liquid: Pumped liquid: Water Liquid temperature range: 253 .. 393 K Liquid temp: 293 K Density: 998.2 kg/m³ Technical: Speed for pump data: 2896 rpm Rated flow: 5.8 m³/h Rated head: 51.8 m Shaft seal: HQQE Approvals on nameplate: CE, TR Curve tolerance: ISO 9906:1999 Annex A Materials: Pump housing: Stainless steel DIN W.-Nr. 1.4408 ASTM A 351 CF 8M Impeller: Stainless steel DIN W.-Nr. 1.4301 AISI 304 Installation: Maximum ambient temperature: 333 K Max pressure at stated temp: 25 bar / 120 °C 25 bar / -20 °C Flange standard: DIN Pipe connection: DN 25 / DN 32 Pressure stage: PN 16 / PN 25 Flange size for motor: FT115 Electrical data: Motor type: 90SB IE Efficiency class: IE3 Number of poles: 2 Rated power - P₂: 1.5 kW Power (P₂) required by pump: 1.5 kW Mains frequency: 50 Hz Rated voltage: 3 x 220-240 D/380-415 Y V Rated current: 5,45/3,15 A Starting current: 850-930 % Cos phi - power factor: 0,87-0,82 Rated speed: 2890-2910 rpm Efficiency: IE3 84,2% Motor efficiency at full load: 84,2-84,2 % Motor efficiency at 3/4 load: 84,5-83,9 %

Position	Qty.	Description
		Motor efficiency at 1/2 load: 83,1-81,0 % Enclosure class (IEC 34-5): 55 (Protect. water jets/dust) Insulation class (IEC 85): F Others: Label: Grundfos Blueflux Minimum efficiency index, MEI $\geq$: 0.57 Net weight: 36.8 kg Gross weight: 40.8 kg Shipping volume: 0.08 m3

96528006 CRI 5-10 50 Hz



Description	Value
Product name:	CRI 5-10 A-FGJ-I-E-HQQE
Product No:	96528006
EAN number:	5700397105795

Technical:

Speed for pump data:	2896 rpm
Rated flow:	5.8 m³/h
Rated head:	51.8 m
Impellers:	10
Shaft seal:	HQQE
Approvals on nameplate:	CE,TR
Curve tolerance:	ISO 9906:1999 Annex A
Stages:	10
Pump version:	A
Model:	A

Materials:

Pump housing:	Stainless steel
	DIN W.-Nr. 1.4408
	ASTM A 351 CF 8M
Impeller:	Stainless steel
	DIN W.-Nr. 1.4301
	AISI 304
Material code:	I
Code for rubber:	E

Installation:

Maximum ambient temperature:	333 K
Max pressure at stated temp:	25 bar / 120 °C
	25 bar / -20 °C
Flange standard:	DIN
Connect code:	FGJ
Pipe connection:	DN 25 / DN 32
Pressure stage:	PN 16 / PN 25
Flange size for motor:	FT115




Liquid:

Pumped liquid:	Water
Liquid temperature range:	253 .. 393 K
Liquid temp:	293 K
Density:	998.2 kg/m ³

Electrical data:


Motor type:	90SB
IE Efficiency class:	IE3
Number of poles:	2
Rated power - P2:	1.5 kW
Power (P2) required by pump:	1.5 kW
Mains frequency:	50 Hz
Rated voltage:	3 x 220-240 D/380-415 Y V
Rated current:	5,45/3,15 A
Starting current:	850-930 %
Cos phi - power factor:	0,87-0,82
Rated speed:	2890-2910 rpm
Efficiency:	IE3 84,2%
Motor efficiency at full load:	84,2-84,2 %
Motor efficiency at 3/4 load:	84,5-83,9 %
Motor efficiency at 1/2 load:	83,1-81,0 %
Enclosure class (IEC 34-5):	55 (Protect. water jets/dust)
Insulation class (IEC 85):	F
Motor protec:	NONE
Motor No:	85U05906

Others:




Description	Value
Label:	Grundfos Blueflux
Minimum efficiency index, MEI ≥:	0.57
Net weight:	36.8 kg
Gross weight:	40.8 kg
Shipping volume:	0.08 m3

96528006 CRI 5-10 50 Hz



Note! All units are in [mm] unless others are stated.
Disclaimer: This simplified dimensional drawing does not show all details.

96528006 CRI 5-10 50 Hz



Note! All units are in [mm] unless others are stated.

*Disclaimer: The information about the Grundfos pump in this document may be outdated.
Data may be subject to alterations without further notice.
Please contact us to verify the data above is still accurate/up-to-date.*

All information is copyright Grundfos.



info@lenntech.com

www.lenntech.com

tel. +31-15-261.09.00

fax. +31-15-261.62.89